

Servinox

Garanti: 12 ay
Bu ¼r¼ne ait T¼rkiye i¼i kapı teslim fiyat ve teslim s¼resi i¼eren teklifimizi almak i¼in **info@yursat.com.tr** e-posta adresine başvuru yapabilir ya da ayrıntılı bilgi i¼in +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaşabilirsiniz.
Servinox Markası, tedarik s¼resi i¼in l¼tfen bizimle iletiőime ge¼iniz.

Firmamız Servinox T¼rkiye Distrib¼t¼r¼ veya temsilcisi deęildir. Firmamız sipariő durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.



¼r¼n	A¼ıklama
ZJM10600	Lot 10x Membranes SILICONE pour PEMS DN10
305.11.00	
BO40619	
DOSTECHTRACA	
JI30670250	
JI30820200	
JM00610	
JM05301	
JM38605I	
JM82605I	
JR00306	
JR00316	

JR00323
JR00330A
JR00332
JR00337
JR00339
JR00345
JR00351
JR00359
LPA25FMBE/0009
LPAA25FCBE/0112
LPAA25FCBE/0113
MB3004003525
PEMC150011010S
PEMS060021000E
PEMS060221000S
RP401001
RP82469/0001
RPF823116ECS1D/001
RW 20170110510
RW 20180150500
RW 20250200695
RW 20270250770
TJ25201
TJ25301
TJ25401
ZHSV88085/0111
ZRP401002E
ZTCRP401001
ZTCRP82469
PEMS DN06/EPDM flared to be w/x1 smooth PEMS type manual sampling valve Instantaneous dismantling of head

PEMS060011000E	and diaphragm Diameter : DN06 Operating temperature: +1°C to 120°C Operating pressure: from 0.1 to 6.0 bar Intake connection : Flared body to weld Ø24,5 Outlet connection : Smooth nozzle to be welded Ø8 x 1mm Flame sterilization 1.4404 stainless steel – EPDM membrane compliant with FDA CFR 21.177.2600 and 1935/2004/CE regulation. Old reference PES06651E
PEMS100021000E	Sample valve II 1.4404 plain /plain ND06 Manual sampling Valve Type PEMS Disassembly of the screwed head and the diaphragm. Operating temperatures: +1° C to +120° C Service Pressure: from 0.1bar to 6 bar Diameter: DN10 Inlet connection: smooth weld (Ø18 mm) Sampling output connection: Smooth-welded (Ø12 x 1 mm) BENDED Flame sterilization Stainless steel grade 1.4404 - EPDM membrane in compliance with FDA CFR 21.177.2600 and Regulation 1935/2004 / EC Ancienne Référence PES10151E
PEMS060501000E	PEMS DN06/EPDM CL/OD1"/x1PLAIN PEMS type manual sampling valve Instantaneous dismantling of head and diaphragm Diameter : DN06 Operating temperature: +1°C to 120°C Operating pressure: from 0.1 to 6.0 bar Intake connection : Flared Clamp OD 1" Outlet connection : Smooth nozzle to be welded Ø8 x 1mm Flame sterilization 1.4404 stainless steel – EPDM membrane compliant with FDA CFR 21.177.2600 and 1935/2004/CE regulation. Ancienne Référence PES06651E/0005 OU PES06207
PEMS iii T W/W 8*1+CA	
liste	
seal	
Jr 00339 Epdm R Gasket	
Jm 05300	
Jm05301 Membrane	
Zhsv88085	
Service-Kit Forhsv88085\0111svx260197\4dn250	
Jf 00330a	
Jm05601	
Mb3004003525 (Epdm Diaphragm)	
Jm00610 Cap, Silicon Quality For Pems Dn 06 Outlet	
Jr 00306 Epdm R Gasket	
Ji 30670250 Epdm I Gasket	
Tj 25301 Spring	

[Jm38605i Part Pigging Systemmagnetic
Silicone Pig50shore, Insert Htfor Tube
38,1x1,5](#)

[Ji 30820200 Epdm I Gasket](#)

[Pems06002100e Probenahmeventil Typ
Pems I](#)

[Tj 25401 Gasket](#)

[Tj 25201 Clapper](#)

[Bo 40619 Coupling Rod](#)

[Pems060021010s](#)

[Jr 00316 Epdm R Gasket](#)