

Sweco

Garanti: 12 ay
Bu ¼r¼ne ait T¼rkiye i¼i kapı teslim fiyat ve teslim s¼resi i¼eren teklifimizi almak i¼in info@yursat.com.tr e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi i¼in +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.
Sweco Markası, tedarik s¼resi i¼in l¼tfen bizimle iletiŐime ge¼iniz.

Firmamız Sweco T¼rkiye Distrib¼t¼r¼ veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.



¼r¼n	A¼ıklama
00-00000306	
06W009900A	
24A8A074T	
48A5A034T	
48A5A046T	
48A3A100M	
48A3A180M	
62 MKM	
72R8A165T	
77 MKM	
E02C18236N	
GS0E80000-02	

GS5S80102-01	
GS5S80553-01	
LS24 43 MKM	
LS24S	
P60K00600-012	
P60K00602-012	
S30S00200	
S30W01904	
S48K00226	Spring spool type for use in a SWECO separator
S48K00990	
S48X01904T	
S60S00201	Spiral springs for use in a SWECO separator Wire diameter 6.4 mm Stainless steel AISI 304, material 1.4301
S60W11104	
S60W81104	
S72X01904	
GS5C80350-10AE	Classifier suspension
GH3409610324701	GYRA SCREEN, 34-1/2 OCW X 96, 5/16 CLOP .047 WD, 304SS
GH34096010SXX02	GYRA SCREEN, 34-1/2 OCW X 96, 10 MESH .025 WD, 304SS
GS4K80010-01	Bearing Assembly
S72W01904	Flexible connection sleeve 10" (254 mm) for SWECO separator 10" ID x 10.5" LG (ø 254 mm x 267 mm long) Material neoprene white FDA compliant Wall thickness 3 mm Temperature range -15 °C to 100 °C For inlet lid and outlet frame
Cleaning balls for SWECO separator	
	Single-deck system for screening into two fractions, ready to use: Key data: Ø machine approx. 800 mm Ø machine base approx. 606 mm Height of the machine without lid approx. 785 mm Height of the machine with lid approx. 938 mm Weight of the machine approx. 154 kg (plus lid approx. 12 kg) Noise level when idling: approx. 82 dB(A) Motor: Motor power 0.37 kW (1/2 HP), 3 phases, 50 Hz Speed 1,450 rpm, Voltage 220-240 / 380-415 Volts Protection class IP65 Machine base & machine table: Round closed machine base with internal motor. The engine is accessible through a door on the base. The machine table holds the motor and is mounted on stainless steel springs on the base, so that the

Round sieve machine model CL30S66WC (30" Ø800 mm)	system can oscillate freely. Material: Machine base and machine table in mild steel / carbon steel S275JR, glass bead blasted (SA 2.5) primed with white epoxy clear varnish (approx. 120 µm thickness in Average) coated. SWECO standard paint finish: RAL9010 (special paint finish on customer request against surcharge). All parts in contact with the product are made of material 1.4301, stainless steel AISI 304, glass bead blasted without painting. All non-metallic and Materials in contact with the product: see description. The screen frames are located on the machine table: A 6" (153 mm) high table frame with a spout size 4" x 6" (101 mm x 153 mm) A 6" (153 mm) high filling frame with a 4" x 6" (101 mm x 153 mm) outlet. 4. Adjustments / additional components
GS5C80350-10AE	Suspension element for a SWECO Gyrotory Separator
Ls24s Ultrasound Kit For Ls24s For Connection To Two Sections	
P60k00600-010 Prom Patrol - Inside F6 Inch, Length 12 Inches.	
S24b00704	CONTROL
48a3a100m	
00-00000224	
Gs5s80553-01 Clamp For Sieve On The Discharge Side	
S48w01904 8" Id X 12" Lg Connector White Neoprene	
Xs 60	
S72x01904 Corrugated Sleeves Silicone 10" Id X 10.5" Lg (D254 Mm, Length - 260 Mm)- Silicone	
E05c48051n	MOTOR
62 ???	
77 ???	
Gs5s80102-01 Sieve Clamp On The Loading Side	
48a3a180m	
S60r11104	
03w009900a	
48?3?180?	
24?8?074?	

[S48w01904](#)

[P60k00602-012 Inside F8 Tube Sleeve,
Length 10 Inches](#)

[48?3?100?](#)

[Gs0e80000-02 Ball White Epdm Dia: 1-
3/8 \(35 Mm\)material Neopren Weiss](#)

[Ls24 43 ???](#)